



WNA160B

**cubyko Schuko Socket composable white IP55**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Functions**

Integrated earth fault protection	No
Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

**Configuration**

Number of modules	1
-------------------	---

**Compatibility**

IFTTT support available	No
-------------------------	----

**Controls and indicators**

Indicator lamp	no
With or without indicator	without

**Connectivity**

With USB charging socket	No
--------------------------	----

**Main electrical features**

Nominal voltage	250 V
Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	64 mm
Depth of installed product	22.8 mm
Height of installed product	81 mm
Width of installed product	75 mm
Height	81 mm
Width	81 mm

**Capacity**

Number of modules for WA	2
Number of module locations	2

<b>Cover, door</b>	
Interlockable	No
<b>Power supply</b>	
Special power supply	No special power supply
<b>Materials</b>	
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Surface appearance	satin finish
Transparent	No
Metallic colour	No
<b>Connection</b>	
Number of accessible phases	1
Type of connection	Quickconnect
<b>Accessories included</b>	
With miniature fuse	No
<b>Equipment</b>	
Number of units	1
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
<b>Standards</b>	
Approvals	NFC 61314
<b>Safety</b>	
IK protection code against mechanical impacts	07
Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes
<b>Identification</b>	
Version	F