



WNA160B

cubyko Schuko Socket composable white IP55

Technical properties

Architecture

Type of pole	SCHUKO
Fixing mode	Clipped

Functions

Integrated earth fault protection	No
Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

Configuration

Number of modules	1
-------------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V
Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	64 mm
Depth of installed product	22.8 mm
Height of installed product	81 mm
Width of installed product	75 mm
Height	81 mm
Width	81 mm

Capacity

Number of modules for WA	2
--------------------------	---

Cover, door

Interlockable	No
---------------	----

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material quality	thermoplastic
------------------	---------------

Surface appearance	satin finish
--------------------	--------------

Surface protection	other
--------------------	-------

Transparent	No
-------------	----

Metallic colour	No
-----------------	----

Installation, mounting

Fixing type	turn screw lock
-------------	-----------------

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
------------------------------------	---

Number of accessible phases	1
-----------------------------	---

Phase pickup	L1
--------------	----

Type of connection	Quickconnect
--------------------	--------------

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of units	1
-----------------	---

Number of socket outlets switchable	0
-------------------------------------	---

On/Off switch	No
---------------	----

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
---	----

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Protection	without protective screen
------------	---------------------------

Use conditions

Operating temperature	-15...30 °C
-----------------------	-------------

Storage/transport temperature	-50...50 °C
-------------------------------	-------------

Insulated	Yes
-----------	-----

Identification

Range	cubyko
Version	F
