



WNA300

## Cubyko LT shutter switch with arrow symbol composable grey IP55

### Technical properties

#### Architecture

Fixing mode Clipped

#### Controls and indicators

Indicator lamp no

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Rated current 10 AX

#### Dimensions

Depth of installed product 40 mm

Height of installed product 75 mm

Width of installed product 75 mm

#### Capacity

Number of modules for WA 2

#### Materials

RAL colour RAL 7011 - Iron grey

Material polypropylène

#### Equipment

Heating switch No

#### Safety

IK protection code against mechanical impacts 07

Protection index IP IP20

Impact strength IK07

#### Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

#### Identification

Range cubyko

Composition Mechanism with upper casing

#### Pictograms

