



WNA301

cubyko Shutter PB compos. grey

Technical properties

Architecture

Type of order	Switch
Type of control unit	double push button
Fixing mode	Clipped

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Fixing type	turn screw lock
Mounting type	flush mounted / surface mounted

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	2 way
Type of connection	Quickconnect

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
---	----

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing

Pictograms

Symbole WA	INSTALLATEUR.JPG
------------	------------------