



WNA301

cubyko Shutter PB compos. grey

Technical properties

Architecture

Fixing mode Clipped

Controls and indicators

Indicator lamp no

Main electrical features

Frequency 50/60 Hz

Electric current

Rated current 10 A

Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 40 mm

Height of installed product 75 mm

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

RAL colour RAL 7011 - Iron grey

Material polypropylène

Material Mixed materials

Connection

Type of connection Quickconnect

Safety

IK protection code against mechanical impacts 07

Protection index IP IP55

Impact strength IK07

Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

Identification

Range cubyko

Composition Mechanism with upper casing

