



WNA301B

**Cubyko LT shutter push-button with stop symbol composable white IP55**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Controls and indicators**

Indicator lamp no

**Main electrical features**

Frequency 50/60 Hz

**Electric current**

Rated current 10 A

**Dimensions**

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 40 mm

Height of installed product 75 mm

Width of installed product 75 mm

**Capacity**

Number of modules for WA 2

**Materials**

RAL colour RAL 9010 - Pure white

Material polypropylène

**Safety**

IK protection code against mechanical impacts 07

Protection index IP IP20

Impact strength IK07

**Use conditions**

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

**Identification**

Range cubyko

Composition Mechanism with upper casing