



WNA601

cubyko Light signalisation compasable red/green

Technical properties

Functions

With function lighting	Yes
------------------------	-----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Electric current

Rated current	16 A
---------------	------

Power

Power absorbed	1.4 mW
----------------	--------

Capacity

Number of modules for WA	2
--------------------------	---

Lighting control

Type of lamp	LED
--------------	-----

Installation, mounting

Fixing type	Clipped
-------------	---------

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

Connection

Lamp socket type	Fix
------------------	-----

Equipment

With lighting	Yes
---------------	-----

Standards

Approvals	NF
-----------	----

Safety

IK protection code against mechanical impacts	07
---	----

Identification

Range	cubyko
-------	--------