



WNA601

cubyko Light signalisation compasable red/green

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With function lighting Yes

Main electrical features

Nominal voltage 250 V

Electric current

Rated current 16 A

Power

Power absorbed 1.4 mW

Capacity

Number of modules for WA 2

Materials

RAL colour RAL 7011 - Iron grey

Material Polypropylen

Type of surface treatment mat varnish

Lighting control

Type of lamp LED

Installation, mounting

Fixing type Clipped

Mounting type flush mounted / surface mounted

Connection

Lamp socket type Fix

Equipment

With lighting Yes

Standards

Approvals NF

Safety

IK protection code against mechanical impacts 07

