



WNA602

cubyko Light signalisation composable blue

Technical properties

Functions

With function lighting Yes

Main electrical features

Nominal voltage 250 V

Electric current

Rated current 16 A

Power

Power absorbed 1.6 mW

Capacity

Number of modules for WA 2

Lighting control

Type of lamp LED

Installation, mounting

Fixing type Clipped

Mounting type flush mounted / surface mounted

Connection

Lamp socket type Fix

Equipment

With lighting Yes

Safety

IK protection code against mechanical impacts 07

Identification

Range cubyko