



WNC001

**cubyko 2-way switch wall mounted grey IP55**

**Technical properties**

**Architecture**

Type of order	Switch
Type of control unit	single rocker
Number of keys	1
Fixing mode	Screwed

**Controls and indicators**

Indicator lamp	no
----------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x61
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

Colour	complete grey
RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Mixed materials
Type of surface treatment	mat

**Installation, mounting**

Mounting type	surface
---------------	---------

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	2 way
Type of connection	Quickconnect

**Standards**

**Safety**

---

IK protection code against mechanical impacts 07

---

Protection index IP IP55

**Identification**

---

Range W.1

---

Composition Complete installation with frame