



WNC001

cubyko 2-way switch wall mounted grey IP55

Technical properties

Architecture

Type of order	Switch
Type of control unit	single rocker
Number of keys	1

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwxh)	76x76x61
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Mounting type	surface
---------------	---------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	2 way
Type of connection	Quickconnect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
-----------------------------------------------	----

Identification

Range

W.1

Composition

Complete installation with frame