



WNC003

**cubyko 2-way switch with control light with neutral wall mounted grey IP55**

**Technical properties**

**Architecture**

Type of control unit	single rocker
Number of keys	1
Fixing mode	Screwed

**Main electrical features**

Frequency	50/60 Hz
-----------	----------

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x65
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

RAL colour	RAL 7011 - Iron grey
Material	polypropylène

**Connection**

Type of connection	Quickconnect
--------------------	--------------

**Safety**

IK protection code against mechanical impacts	07
Protection index IP	IP55

**Identification**

Range	W.1
Composition	Complete installation with frame