



WNC003

**cubyko 2-way switch with control light with neutral wall mounted grey IP55**

**Technical properties**

**Architecture**

Type of order	Switch
Type of control unit	single rocker
Number of keys	1

**Controls and indicators**

Indicator lamp	as an accessory
----------------	-----------------

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x65
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

Material	polypropylène
----------	---------------

**Installation, mounting**

Mounting type	surface
---------------	---------

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	2 way
Type of connection	Quickconnect

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

IK protection code against mechanical impacts	07
---	----

**Identification**

---

Range

W.1

---

Composition

Complete installation with frame