



WNC021

**cubyko Push-button 10/1F with light wall mounted grey IP55**

**Technical properties**

**Architecture**

Type of order	Push button
Type of control unit	Push button
Number of keys	1

**Controls and indicators**

Indicator lamp	yes
----------------	-----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x71
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

Material	polypropylène
----------	---------------

**Installation, mounting**

Fixing type	With screws
Mounting type	surface

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	1NC+1NO
Type of connection	Quickconnect

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

IK protection code against mechanical impacts	07
---	----

**Identification**

---

Range

W.1

---

Composition

Complete installation with frame