



WNC021

cubyko Push-button 10/1F with light wall mounted grey IP55

Technical properties

Architecture

Number of keys	1
Fixing mode	Screwed

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 A
---------------	------

Dimensions

Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwxhh)	76x76x71
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 7011 - Iron grey
Material	polypropylène

Connection

Type of connection	Quickconnect
--------------------	--------------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55

Identification

Range	W.1
Composition	Complete installation with frame