



WNC023

Cubyko LT push-button 1F with control light wall mounted grey IP55

Technical properties

Architecture

Number of keys	1
----------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x75
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	quick connect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes

Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Identification	
Range	cubyko
Composition	Complete installation with frame
Pictograms	
Symbole WA	INSTALLATEUR.JPG