



WNC023

Cubyko LT push-button 1F with control light wall mounted grey IP55

Technical properties

Architecture

Number of keys 1

Controls and indicators

Indicator lamp yes

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 10 A

Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 64 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 76x76x75

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

Material polypropylène

Installation, mounting

Fixing type With screws

Mounting type flush-mounted

Connection

Connection cross-sect. rigid cable mini 2x1 mm² - maxi 2x2,5 mm²

Type of connection quick connect

Standards

Approvals EN 60669-1

Safety

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform Yes

Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Identification	
Range	cubyko
Composition	Complete installation with frame
Pictograms	
Symbole WA	INSTALLATEUR.JPG