



WNC023

Cubyko LT push-button 1F with control light wall mounted grey IP55

Technical properties

Architecture

Number of keys	1
Fixing mode	Screwed

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x75
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 7011 - Iron grey
------------	----------------------

Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

Connection

Type of connection	quick connect
--------------------	---------------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Pictograms

Symbole WA

INSTALLATEUR.JPG