



WNC025

Cubyko LT push-button 1F with label holder wall mounted grey IP55

Technical properties

Architecture

Number of keys	1
Fixing mode	Screwed

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwxhh)	76x76x77
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 7011 - Iron grey
Material	polypropylène

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Complete installation with frame

Pictograms

