



WNC025

## Cubyko LT push-button 1F with label holder wall mounted grey IP55

### Technical properties

#### Architecture

Number of keys 1

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Nominal voltage 24V

Frequency 50/60 Hz

#### Electric current

Rated current 10 A

#### Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 64 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 76x76x77

Width of installed product 75 mm

#### Capacity

Number of modules for WA 2

#### Materials

Material polypropylène

#### Installation, mounting

Fixing type With screws

Mounting type flush-mounted

#### Connection

Connection cross-sect. rigid cable mini 2x1 mm<sup>2</sup> - maxi 2x2,5 mm<sup>2</sup>

Type of connection quick connect

#### Standards

Approvals EN 60669-1

#### Safety

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform Yes

Halogen free	No
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
<b>Identification</b>	
Range	cubyko
Composition	Complete installation with frame
<b>Pictograms</b>	
Symbole WA	INSTALLATEUR.JPG