



WNC036

cubyko Key switch 3 positions wall mounted grey IP55

Technical properties

Architecture

Type of control unit	Key
Number of keys	1
Fixing mode	Screwed

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	74 mm
Height of installed product	75 mm
Dimensions (LLxwxh)	76x76x81
Width of installed product	75 mm

Materials

RAL colour	RAL 7011 - Iron grey
Material	polypropylène

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

