



WNC044

cubyko Double PB NO/NF wall M grey

Technical properties

Architecture

Type of order	Push button
Type of control unit	double push button
Number of keys	2

Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x87
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Fixing type	With screws
Mounting type	surface

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	Quickconnect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Complete installation with frame