



WNC100

cubyko Socket 2P+E screwless wall mounted grey IP55

Technical properties

Architecture

Type of pole 2P+T

Functions

Centralized terminal connections No

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 2

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket No

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Depth of installed product 22.8 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 76x76x88

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Number of module locations 2

Cover, door

Interlockable No

Power supply

Materials

Surface appearance	satin finish
Transparent	No

Installation, mounting

Fixing type	With screws
Mounting type	surface

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Phase pickup	L1
Type of connection	Quickconnect

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
Protection	without protective screen

Use conditions

Insulated	Yes
-----------	-----

Identification

Range	W.1
-------	-----
