



WNC122

cubyko Double horizontal socket 2P+E screwless wall mounted grey IP55

Technical properties

Architecture

Fixing mode Screwed

Functions

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 4

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket No

Main electrical features

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Depth of installed product 42.5 mm

Height of installed product 45 mm

Dimensions (LLxwwxhh) 76x76x95

Width of installed product 90 mm

Capacity

Number of modules for WA 4

Number of module locations 4

Cover, door

Interlockable No

Power supply

Special power supply No special power supply

Materials

RAL colour	RAL 7011 - Iron grey
Transparent	No
Metallic colour	No

Connection

Type of connection	Quickconnect
--------------------	--------------

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

Identification

Range	cubyko
-------	--------