



WNC122B



**cubyko Double horizontal socket 2P+E screwless wall mounted white IP55**

**Technical properties**

**Architecture**

Fixing mode Screwed

**Functions**

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

**Configuration**

Number of modules 4

**Compatibility**

IFTTT support available No

**Controls and indicators**

Indicator lamp no

With or without indicator without

**Connectivity**

With USB charging socket No

**Main electrical features**

Frequency 50/60 Hz

**Electric current**

Rated current 16 A

**Dimensions**

Depth of installed product 22.8 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 76x76x96

Width of installed product 146 mm

**Capacity**

Number of modules for WA 4

Number of module locations 4

**Cover, door**

Interlockable No

**Power supply**

Special power supply No special power supply

**Materials**

RAL colour	RAL 9010 - Pure white
Transparent	No
Metallic colour	No

**Connection**

Type of connection	Quickconnect
--------------------	--------------

**Accessories included**

With miniature fuse	No
---------------------	----

**Equipment**

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

**Safety**

IK protection code against mechanical impacts	07
Protection index IP	IP55

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

**Identification**

Range	cubyko
-------	--------