



WNC122B



cubyko Double horizontal socket 2P+E screwless wall mounted white IP55

Technical properties

Architecture

Type of pole	2P+T
--------------	------

Functions

Centralized terminal connections	Yes
With orientation lighting	No
Overvoltage protection	No

Configuration

Number of modules	4
-------------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth of installed product	22.8 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x96
Width of installed product	146 mm

Capacity

Number of modules for WA	4
Number of module locations	4

Cover, door

Interlockable	No
---------------	----

Power supply

Special power supply

No special power supply

Materials

RAL colour	RAL 9010 - Pure white
Surface appearance	satın finish
Surface protection	other
Transparent	No
Metallic colour	No

Installation, mounting

Fixing type	With screws
Mounting type	surface

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Phase pickup	L1
Type of connection	Quickconnect

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without protective screen

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

Identification

Range	cubyko
-------	--------