



WNC123

cubyko Triple horizontal socket 2P+E screwless wall mounted grey IP55

Technical properties

Architecture

Type of pole	2P+T
Fixing mode	Screwed

Functions

Centralized terminal connections	Yes
With orientation lighting	No
Overvoltage protection	No

Configuration

Number of modules	6
-------------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth of installed product	42.5 mm
Height of installed product	45 mm
Dimensions (LLxwwxhh)	76x76x97
Width of installed product	135 mm

Capacity

Number of modules for WA	6
Number of module locations	6

Cover, door

Interlockable	No
---------------	----

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

Colour	complete grey
Colour	grey (shades)
RAL colour	RAL 7011 - Iron grey
Material	Polypropylen
Surface appearance	satin finish
Surface protection	other
Type of surface treatment	mat varnish
Transparent	No
Metallic colour	No

Installation, mounting

Fixing type	With screws
Mounting type	surface

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Phase pickup	L1
Type of connection	Quickconnect

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55
Protection	without protective screen

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

Identification

Range	cubyko
-------	--------