



WNC132B

**cubyko Double vertical socket 2P+E screwless wall mounted white IP55**

**Technical properties**

**Architecture**

Type of pole 2P+T

**Functions**

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

**Configuration**

Number of modules 4

**Compatibility**

IFTTT support available No

**Controls and indicators**

Indicator lamp no

With or without indicator without

**Connectivity**

With USB charging socket No

**Main electrical features**

Nominal voltage 250 V

Frequency 50/60 Hz

**Electric current**

Rated current 16 A

**Dimensions**

Depth of installed product 22.8 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 76x76x100

Width of installed product 75 mm

**Capacity**

Number of modules for WA 4

Number of module locations 4

**Cover, door**

Interlockable No

**Power supply**

Special power supply

No special power supply

### Materials

RAL colour	RAL 9010 - Pure white
Surface appearance	satın finish
Surface protection	other
Transparent	No
Metallic colour	No

### Installation, mounting

Fixing type	With screws
Mounting type	surface

### Connection

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Phase pickup	L1
Type of connection	Quickconnect

### Accessories included

With miniature fuse	No
---------------------	----

### Equipment

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

### Standards

Approvals	NFC 61314
-----------	-----------

### Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without protective screen

### Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

### Identification

Range	cubyko
-------	--------