



WNC132B

cubyko Double vertical socket 2P+E screwless wall mounted white IP55

Technical properties

Architecture

Type of pole 2P+T

Functions

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 4

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket No

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Depth of installed product 22.8 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 76x76x100

Width of installed product 75 mm

Capacity

Number of modules for WA 4

Number of module locations 4

Cover, door

Interlockable No

Power supply

Special power supply

No special power supply

Materials

RAL colour	RAL 9010 - Pure white
Surface appearance	satın finish
Surface protection	other
Transparent	No
Metallic colour	No

Installation, mounting

Fixing type	With screws
Mounting type	surface

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Phase pickup	L1
Type of connection	Quickconnect

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without protective screen

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

Identification

Range	cubyko
-------	--------