



WNC160

**cubyko Socket Schuko screwless & childpro wall mounted grey IP55**

**Technical properties**

**Architecture**

Type of pole	SCHUKO
--------------	--------

**Functions**

Integrated earth fault protection	No
Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

**Configuration**

Number of modules	2
-------------------	---

**Compatibility**

IFTTT support available	No
-------------------------	----

**Controls and indicators**

Indicator lamp	no
With or without indicator	without

**Connectivity**

With USB charging socket	No
--------------------------	----

**Main electrical features**

Nominal voltage	250 V
Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	63 mm
Depth of installed product	22.8 mm
Height of installed product	76 mm
Length	45 mm
Dimensions (LLxwxhh)	76x76x103
Width of installed product	45 mm
Height	76 mm
Width	76 mm

**Capacity**

Number of modules for WA	2
Number of module locations	2
<b>Cover, door</b>	
Interlockable	No
<b>Power supply</b>	
Special power supply	No special power supply
<b>Materials</b>	
Material quality	thermoplastic
Surface appearance	satin finish
Surface protection	other
Transparent	No
Metallic colour	No
<b>Installation, mounting</b>	
Fixing type	With screws
Mounting type	surface
<b>Connection</b>	
Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Number of accessible phases	1
Phase pickup	L1
Type of connection	Quickconnect
<b>Accessories included</b>	
With miniature fuse	No
<b>Equipment</b>	
Number of units	2
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
<b>Standards</b>	
Approvals	NFC 61314
<b>Safety</b>	
IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without protective screen
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

**Identification**

---

Range	cubyko
Version	F

---