



WNC160

cubyko Socket Schuko screwless & childpro wall mounted grey IP55

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Functions

Integrated earth fault protection	No
Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

Configuration

Number of modules	2
-------------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	63 mm
Depth of installed product	22.8 mm
Height of installed product	76 mm
Length	45 mm
Dimensions (LLxwwxhh)	76x76x103
Width of installed product	45 mm
Height	76 mm
Width	76 mm

Capacity

Number of modules for WA	2
--------------------------	---

Cover, door

Interlockable	No
---------------	----

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

RAL colour	RAL 7011 - Iron grey
------------	----------------------

Transparent	No
-------------	----

Metallic colour	No
-----------------	----

Connection

Number of accessible phases	1
-----------------------------	---

Type of connection	Quickconnect
--------------------	--------------

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of units	2
-----------------	---

Number of socket outlets switchable	0
-------------------------------------	---

On/Off switch	No
---------------	----

With transparent product label holder	No
---------------------------------------	----

Safety

IK protection code against mechanical impacts	07
---	----

Protection index IP	IP55
---------------------	------

Use conditions

Operating temperature	-15...30 °C
-----------------------	-------------

Storage/transport temperature	-50...50 °C
-------------------------------	-------------

Insulated	Yes
-----------	-----

Identification

Range	cubyko
-------	--------

Version	F
---------	---