



WNE001

cubyko 2-way switch flush mounted grey IP55

Technical properties

Architecture

Type of control unit	single rocker
Fixing mode	Screwed

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	40 mm
Height of installed product	75 mm
Dimensions (LLxwxhh)	83X83X26
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Mixed materials

Connection

Type of connection	Quickconnect
--------------------	--------------

Safety

IK protection code against mechanical impacts	07
---	----

Use conditions

Operating temperature	-40...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing