



WNE001B

**Cubyko LT 2-way switch flush mounted white IP55**

**Technical properties**

**Controls and indicators**

Indicator lamp no

**Main electrical features**

Nominal voltage 250 V

Frequency 50/60 Hz

**Electric current**

Rated current 10 AX

**Dimensions**

Depth of installed product 40 mm

Height of installed product 75 mm

Dimensions (LLxwxhh) 83X83X25

Width of installed product 75 mm

**Capacity**

Number of modules for WA 2

**Materials**

RAL colour RAL 9010 - Pure white

**Installation, mounting**

Mounting type flush-mounted

**Connection**

Connection cross-sect. rigid cable mini 2x1 mm<sup>2</sup> - maxi 2x2,5 mm<sup>2</sup>

Type of connection quick connect

**Equipment**

Heating switch No

**Standards**

Approvals EN 60669-1

**Safety**

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

**Use conditions**

---

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

---

**Identification**

---

Range	cubyko
Composition	Mechanism with upper casing

---