



WNE001B

## Cubyko LT 2-way switch flush mounted white IP55

### Technical properties

#### Controls and indicators

Indicator lamp	no
----------------	----

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Depth of installed product	40 mm
Height of installed product	75 mm
Dimensions (LLxwxhh)	83X83X25
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

#### Installation, mounting

Mounting type	flush-mounted
---------------	---------------

#### Connection

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of connection	quick connect

#### Equipment

Heating switch	No
----------------	----

#### Standards

Approvals	EN 60669-1
-----------	------------

#### Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

**Use conditions**

---

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

---

**Identification**

---

Range	cubyko
Composition	Mechanism with upper casing

---