



WNE001B

Cubyko LT 2-way switch flush mounted white IP55

Technical properties

Architecture

Fixing mode Screwed

Controls and indicators

Indicator lamp no

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 10 AX

Dimensions

Depth of installed product 40 mm

Height of installed product 75 mm

Dimensions (LLxwxhh) 83X83X25

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

RAL colour RAL 9010 - Pure white

Installation, mounting

Mounting type flush-mounted

Connection

Connection cross-sect. rigid cable mini 2x1 mm² - maxi 2x2,5 mm²

Type of connection quick connect

Equipment

Heating switch No

Standards

Approvals EN 60669-1

Safety

IK protection code against mechanical impacts 07

Protection index IP IP20

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Identification

Range

cubyko

Composition

Mechanism with upper casing