



WNE023

cubyko Push-button 1F with control light flush mounted grey IP55

Technical properties

Architecture

Fixing mode Screwed

Controls and indicators

Indicator lamp yes

Main electrical features

Frequency 50/60 Hz

Electric current

Rated current 10 A

Dimensions

Depth of installed product 40 mm

Height of installed product 75 mm

Dimensions (LLxwxhh) 83X83X30

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

RAL colour RAL 7011 - Iron grey

Material polypropylène

Connection

Type of connection Quickconnect

Safety

IK protection code against mechanical impacts 07

Use conditions

Operating temperature -40...30 °C

Storage/transport temperature -50...50 °C

Identification

Range cubyko

Composition Mechanism with upper casing