



WNE023

**Cubyko LT push-button 1F with control light flush mounted grey IP55**

**Technical properties**

**Controls and indicators**

Indicator lamp	yes
----------------	-----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	83X83X30
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Installation, mounting**

Fixing type	With screws
Mounting type	flush-mounted

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of connection	quick connect

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

**Use conditions**

Operating temperature	-15...30 °C
-----------------------	-------------

Storage/transport temperature

-50...50 °C

---

**Identification**

Range

cubyko

Composition

Mechanism with upper casing

---

**Pictograms**

Symbole WA

INSTALLATEUR.JPG