



WNE023B

cubyko Push-button 1F with control light flush mounted white IP55

Technical properties

Architecture

Type of order	Push button
Type of control unit	Push button

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Depth of installed product	40 mm
Height of installed product	75 mm
Dimensions (LLxwxhh)	83X83X29
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Fixing type	With screws
Mounting type	flush

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	Quickconnect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
---	----

Use conditions

Operating temperature	-40...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing
