



WNE023B

cubyko Push-button 1F with control light flush mounted white IP55

Technical properties

Architecture

Type of order	Push button
Type of control unit	Push button
Fixing mode	Screwed

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Depth of installed product	40 mm
Height of installed product	75 mm
Dimensions (LLxwxh)	83X83X29
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	flush white
RAL colour	RAL 9010
Material	polypropylène
Material	Polypropylen
Type of surface treatment	mat

Installation, mounting

Fixing type	With screws
Mounting type	flush

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	Quickconnect

Standards

Safety

IK protection code against mechanical impacts

07

Protection index IP

IP55 (flache Wand, mur plat, flat wall)

Use conditions

Operating temperature

-40...30 °C

Storage/transport temperature

-50...50 °C

Identification

Range

cubyko

Composition

Mechanism with upper casing