



WNE025

**cubyko Push-button 1F with label holder flush mounted grey IP55**

**Technical properties**

**Architecture**

Type of order	Push button
Type of control unit	Push button

**Controls and indicators**

Indicator lamp	yes
----------------	-----

**Main electrical features**

Nominal voltage	24V
Frequency	50/60 Hz

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	83X83X34
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

Material	polypropylène
----------	---------------

**Installation, mounting**

Fixing type	With screws
Mounting type	flush

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	1NC+1NO
Type of connection	Quickconnect

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

IK protection code against mechanical impacts	07
---	----

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

---

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

---

**Identification**

Range	cubyko
Composition	Mechanism with upper casing

---

**Pictograms**

Symbole WA	INSTALLATEUR.JPG
------------	------------------