



WNE025B

**cubyko Push-button 1F with label holder flush mounted white IP55**

**Technical properties**

**Architecture**

Type of order	Push button
Type of control unit	Push button
Fixing mode	Screwed

**Controls and indicators**

Indicator lamp	yes
----------------	-----

**Main electrical features**

Nominal voltage	24V
Frequency	50/60 Hz

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Depth of installed product	40 mm
Height of installed product	75 mm
Dimensions (LLxwxhh)	83X83X33
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

Colour	flush white
RAL colour	RAL 9010
Material	polypropylène
Material	Polypropylen
Type of surface treatment	mat

**Installation, mounting**

Fixing type	With screws
Mounting type	flush

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	1NC+1NO
Type of connection	Quickconnect

**Standards**

**Safety**

---

IK protection code against mechanical impacts

07

Protection index IP

IP55 (flache Wand, mur plat, flat wall)

**Use conditions**

---

Operating temperature

-40...30 °C

Storage/transport temperature

-50...50 °C

**Identification**

---

Range

cubyko

Composition

Mechanism with upper casing