



WNE040

**Cubyko LT 2-gang 2-way switch flush mounted grey IP55**

**Technical properties**

**Controls and indicators**

Indicator lamp as an accessory

**Main electrical features**

Nominal voltage 250 V

Frequency 50/60 Hz

**Electric current**

Rated current 10 AX

**Dimensions**

Depth of installed product 40 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 83X83X38

Width of installed product 75 mm

**Capacity**

Number of modules for WA 2

**Installation, mounting**

Mounting type flush-mounted

**Connection**

Connection cross-sect. rigid cable mini 2x1 mm<sup>2</sup> - maxi 2x2,5 mm<sup>2</sup>

Type of connection quick connect

**Equipment**

Heating switch No

**Standards**

Approvals EN 60669-1

**Safety**

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

**Use conditions**

Operating temperature -15...30 °C

Storage/transport temperature

-50...50 °C

**Identification**

---

Range

cubyko

Composition

Mechanism with upper casing

**Pictograms**

---

Symbole WA

INSTALLATEUR.JPG