



WNE040

Cubyko LT 2-gang 2-way switch flush mounted grey IP55

Technical properties

Controls and indicators

Indicator lamp as an accessory

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 10 AX

Dimensions

Depth of installed product 40 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 83X83X38

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Installation, mounting

Mounting type flush-mounted

Connection

Connection cross-sect. rigid cable mini 2x1 mm² - maxi 2x2,5 mm²

Type of connection quick connect

Equipment

Heating switch No

Standards

Approvals EN 60669-1

Safety

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

Use conditions

Operating temperature -15...30 °C

Storage/transport temperature

-50...50 °C

Identification

Range

cubyko

Composition

Mechanism with upper casing

Pictograms

Symbole WA

INSTALLATEUR.JPG