



WNE040

Cubyko LT 2-gang 2-way switch flush mounted grey IP55

Technical properties

Architecture

Fixing mode Screwed

Main electrical features

Frequency 50/60 Hz

Electric current

Rated current 10 AX

Dimensions

Depth of installed product 40 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 83X83X38

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

RAL colour RAL 7011 - Iron grey

Equipment

Heating switch No

Safety

IK protection code against mechanical impacts 07

Protection index IP IP20

Impact strength IK07

Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

Identification

Range cubyko

Composition Mechanism with upper casing

Pictograms

Symbole WA INSTALLATEUR.JPG