



WNE100

cubyko Socket 2P+E screwless flush mounted grey IP55

Technical properties

Architecture

Type of pole 2P+T

Functions

Centralized terminal connections No

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 2

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

Connectivity

With USB charging socket No

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Depth of installed product 22.8 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 83X83X39

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Number of module locations 2

Cover, door

Lid shape hinge

Interlockable No

Power supply

Materials

| | |
|--------------------|--------------|
| Material quality | Material mix |
| Surface appearance | satin finish |
| Transparent | No |
| Metallic colour | No |

Installation, mounting

| | |
|---------------|-------------|
| Fixing type | With screws |
| Mounting type | flush |

Connection

| | |
|------------------------------------|---|
| Connection cross-sect. rigid cable | mini 2x1 mm ² - maxi 2x2,5 mm ² |
| Phase pickup | L1 |
| Type of connection | Quickconnect |

Accessories included

| | |
|---------------------|----|
| With miniature fuse | No |
|---------------------|----|

Equipment

| | |
|---------------------------------------|----|
| Number of socket outlets switchable | 0 |
| On/Off switch | No |
| With transparent product label holder | No |

Standards

| | |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

Safety

| | |
|---|---------------------------|
| IK protection code against mechanical impacts | 07 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Protection | without protective screen |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -15...30 °C |
| Storage/transport temperature | -50...50 °C |
| Insulated | Yes |

Identification

| | |
|-------|--------|
| Range | cubyko |
|-------|--------|