



WNE100B

cubyko Socket 2P+E screwless flush mounted white IP55

Technical properties

Architecture

Type of pole	2P+T
--------------	------

Functions

Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

Configuration

Number of modules	2
-------------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
----------------	----

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	83X83X40
Width of installed product	75 mm

Capacity

Number of modules for WA	2
Number of module locations	2

Cover, door

Lid shape	hinge
Interlockable	No

Power supply

Special power supply

No special power supply

Materials

RAL colour

RAL 9010 - Pure white

Material quality

Material mix

Surface appearance

satin finish

Transparent

No

Metallic colour

No

Installation, mounting

Fixing type

With screws

Mounting type

flush

Connection

Connection cross-sect. rigid cable

mini 2x1 mm² - maxi 2x2,5 mm²

Phase pickup

L1

Type of connection

Quickconnect

Accessories included

With miniature fuse

No

Equipment

Number of socket outlets switchable

0

On/Off switch

No

With transparent product label holder

No

Standards

Approvals

NFC 61314

Safety

IK protection code against mechanical impacts

07

Protection

without protective screen

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Insulated

Yes

Identification

Range

cubyko