



WNE100B

**cubyko Socket 2P+E screwless flush mounted white IP55**

**Technical properties**

**Architecture**

Type of pole	2P+T
--------------	------

**Functions**

Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

**Configuration**

Number of modules	2
-------------------	---

**Compatibility**

IFTTT support available	No
-------------------------	----

**Controls and indicators**

Indicator lamp	no
----------------	----

**Connectivity**

With USB charging socket	No
--------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	83X83X40
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
Number of module locations	2

**Cover, door**

Lid shape	hinge
Interlockable	No

**Power supply**

Special power supply

No special power supply

**Materials**

RAL colour

RAL 9010 - Pure white

Material quality

Material mix

Surface appearance

satin finish

Transparent

No

Metallic colour

No

**Installation, mounting**

Fixing type

With screws

Mounting type

flush

**Connection**

Connection cross-sect. rigid cable

mini 2x1 mm<sup>2</sup> - maxi 2x2,5 mm<sup>2</sup>

Phase pickup

L1

Type of connection

Quickconnect

**Accessories included**

With miniature fuse

No

**Equipment**

Number of socket outlets switchable

0

On/Off switch

No

With transparent product label holder

No

**Standards**

Approvals

NFC 61314

**Safety**

IK protection code against mechanical impacts

07

Protection

without protective screen

**Use conditions**

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Insulated

Yes

**Identification**

Range

cubyko