



WNE122

**cubyko Double horizontal socket 2P+E screwless flush mounted grey IP55**

**Technical properties**

**Architecture**

Type of pole	2P+T
Fixing mode	Screwed

**Functions**

Centralized terminal connections	Yes
With orientation lighting	No
Overvoltage protection	No

**Configuration**

Number of modules	4
-------------------	---

**Compatibility**

IFTTT support available	No
-------------------------	----

**Controls and indicators**

Indicator lamp	no
With or without indicator	without

**Connectivity**

With USB charging socket	No
--------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	42.5 mm
Height of installed product	45 mm
Dimensions (LLxwxh)	83X83X42
Width of installed product	90 mm

**Capacity**

Number of modules for WA	4
Number of module locations	4

**Cover, door**

Lid shape	hinge
Interlockable	No
<b>Power supply</b>	
Special power supply	No special power supply
<b>Materials</b>	
RAL colour	RAL 7011 - Iron grey
Surface appearance	satin finish
Transparent	No
Metallic colour	No
<b>Installation, mounting</b>	
Fixing type	With screws
<b>Connection</b>	
Type of connection	Quickconnect
<b>Accessories included</b>	
With miniature fuse	No
<b>Equipment</b>	
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
<b>Standards</b>	
Approvals	NFC 61314
<b>Safety</b>	
IK protection code against mechanical impacts	07
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes