



WNE122

cubyko Double horizontal socket 2P+E screwless flush mounted grey IP55

Technical properties

Architecture

Type of pole 2P+T

Functions

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 4

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket No

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 42.5 mm

Height of installed product 45 mm

Dimensions (LLxwwxhh) 83X83X42

Width of installed product 90 mm

Capacity

Number of modules for WA 4

Number of module locations 4

Cover, door

Lid shape hinge

Interlockable	No
---------------	----

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

Material quality	Material mix
Surface appearance	satin finish
Transparent	No
Metallic colour	No

Installation, mounting

Fixing type	With screws
Mounting type	flush

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Phase pickup	L1
Type of connection	Quickconnect

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
Protection	without protective screen

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

Identification

Range	cubyko
-------	--------