



WNE122B

**cubyko Double horizontal socket 2P+E screwless flush mounted white IP55**

**Technical properties**

**Architecture**

Fixing mode Screwed

**Functions**

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

**Configuration**

Number of modules 4

**Compatibility**

IFTTT support available No

**Controls and indicators**

Indicator lamp no

With or without indicator without

**Connectivity**

With USB charging socket No

**Main electrical features**

Frequency 50/60 Hz

**Electric current**

Rated current 16 A

**Dimensions**

Depth of installed product 42.5 mm

Height of installed product 45 mm

Dimensions (LLxwwxhh) 83X83X43

Width of installed product 90 mm

**Capacity**

Number of modules for WA 4

Number of module locations 4

**Cover, door**

Lid shape hinge

Interlockable No

**Power supply**

**Materials**

---

RAL colour	RAL 9010 - Pure white
Transparent	No
Metallic colour	No

---

**Connection**

---

Type of connection	Quickconnect
--------------------	--------------

---

**Accessories included**

---

With miniature fuse	No
---------------------	----

---

**Equipment**

---

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

---

**Safety**

---

IK protection code against mechanical impacts	07
Protection index IP	IP55

---

**Use conditions**

---

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

---

**Identification**

---

Range	cubyko
-------	--------

---